



- B7000 Bundled RESmart® BPAP + Humidifier
- B5500 RESmart® BPAP Integrated Humidifier
- M1020 RESmart® BPAP Air Filter (2 Pack)
- M1019B RESmart® Air Filter Cover – BPAP
- M4510 Humidifier Water Chamber

RESmart® BPAP 25A Auto Bi-Level

- Full Efficacy Data Reporting
- Innovative tracking technology ensures accurate and comfortable therapy
- 4-25 cmH₂O therapy pressure
- Real time audible alert for tubing/mask leak
- REslex® exhalation relief with four comfort settings
- Remote compliance data access with iCode®
- SD Card standard
- Integration with cloud based iCode Connect™
- Embedded memory stores last night's full raw data, 365 nights of user data and more than 30 years of therapy records
- Last night's compliance-therapy snapshot to assist patient with compliance
- Automatic leak and altitude compensation
- Inspiration trigger for automatic start-up
- Quiet operation

Ergonomic Design

- Integrated heated humidifier
- DC 24V powered and infrared controlled humidifier for patient safety and comfort
- Delay-off feature protects the device from humidity hazard
- Backlit LCD display for operation in dark
- Light user buttons with lockup capability

3B Medical, Inc.
21301 US Highway 27 N • Lake Wales, FL 33859
(863) 226-6285 • info@3bproducts.com
www.3Bproducts.com

Dimensions: 8.66 × 7.6 × 4.4" (220 x 194 x 112mm), 12.3" (313 x 194 x 112mm) (with Integrated Heated Humidifier)

Weight: ___ lbs. (2.2 kg), <4.8 lbs. (3 kg) (with Integrated Heated Humidifier)

Environmental

	Operating	Transport and Storage
Temperature	5 to 35°C	-20 to 55°C
Relative Humidity	≤ 80% Non-condensing	≤ 93% Non-condensing
Atmospheric Pressure	860 to 1060 hPa	500 to 1060 hPa

Standards Compliance:

IEC 60601-1 General Requirements for Safety of Medical Electrical Equipment
IEC 60601-1-2 Electromagnetic Compatibility
ISO 17510 Sleep Apnea Breathing Therapy
ISO 8185 General Requirements for Humidification Systems

Electrical:

AC Power Consumption: 100 - 240V AC, 50/60Hz, Max 95VA
Type of Protection Against Electric Shock: Class II Equipment
Degree of Protection Against Electric Shock: Type BF Applied Part

Degree of Protection Against Ingress of Water: Drip Proof, IPX1

Mode of Operation: Continuous

RESmart®	Pressure	Function	Auto Pressure
BPAP 25	4-25cmH ₂ O	S, CPAP	No
BPAP 25A	4-25cmH ₂ O	S, CPAP, AutoS	available

Pressure

IPAP	4 to 25 cmH ₂ O*	±1 cmH ₂ O**
EPAP	4 to 25 cmH ₂ O*	±1 cmH ₂ O**
CPAP	4 to 20 cmH ₂ O	±1 cmH ₂ O**
Ramp Duration	0 to 60 minutes	±10% of the setting
Rise Time	0 to 3***	±25%****

* Limited to 25 cmH₂O when using the Auto feature (only available under AutoS mode).

** Dynamic pressure accuracy is ±1 cmH₂O measured at the patient end of the circuit.

Static pressure accuracy is ±0.5 cmH₂O measured at the patient end of the circuit.

*** The range of values corresponds to tenths of seconds (e.g., a setting of 4 indicates a Rise Time of 0.4 seconds).

**** Measured at the patient end of circuit.

Disposal: Dispose of the device in accordance with local regulations.

Manufacturer: BMC Medical Co., Ltd.

NOTE: specifications subject to change without prior notice.